

PRODUCT DESCRIPTION

CYTEL 325 N resin is a methylated high imino melamine crosslinker supplied in iso-butanol. CYTEL 325 N resin is highly reactive and has a high tendency towards self-condensation providing films with very good hardness, gloss, chemical resistance and outdoor durability. CYTEL 325 N resin is suitable for a wide range of solventborne or waterborne baking applications, such as coil and can coating formulations, automotive primers and topcoats, and general industrial coatings.

BENEFITS

- Very fast cure response
- Medium to high solids
- Low formaldehyde release

APPLICATION AREAS

- General industrial coatings
- Automotive coatings
- Coil and container coatings

PHYSICAL PROPERTIES

Appearance	Clear Liquid	Visual
Non-volatile by wt.	80 ± 2%	Foil 45 min/45°C
Viscosity, 23°C	1300-4000 mPa.s	ISO 3219
Free formaldehyde	< 0.5%	BS-EN-1243-2011
Color, Gardner	≤ 1	ISO 4630-2
Solvent	Isobutanol	

SOLUBILITY

Alcohols	Complete
Esters	Complete
Ketones	Complete
Aromatic hydrocarbons	Partial
Aliphatic hydrocarbons	Insoluble
Water	Partial

COMPATIBILITY

Acrylic resins	Very good
Alkyd resins	Very good
Epoxy resins	Very good
Polyester resins	Very good

BACKBONE POLYMER SELECTION

CYTEL 325 N resin is an effective crosslinker for backbone polymer resins containing hydroxyl, carboxyl, and amide functional groups, such as those found on alkyd, polyester or acrylic resins. Although the optimum level of CYTEL 325 N resin should be determined experimentally, ratios of 25 to 35% based on resin solids are typically most effective.

CATALYSIS

CYTEL 325 N resin may not require the addition of an acid catalyst to the formulation to obtain effective cure. In many instances, the acidity of the backbone polymer in the formulation is sufficient to catalyze the reaction under normal baking conditions (15 - 20 minutes at 120 - 150°C). If catalyst addition is required, then 0.5 - 1.0% of CYCAT® 296-9 catalyst based on total resin solids is recommended.

FORMULATION STABILITY

The stability of solvent-borne systems containing CYTEL 325 N resin can be enhanced by the addition of primary alcohols, amines, or a combination of these. Low molecular weight primary alcohols such as ethanol and n-butanol are most effective. Recommended amines are TEA, DMEA or 2-AMP at a concentration of 0.5 - 1.0% on total binder solids. For best stability in waterborne systems, a pH between 7.5 - 8.5 should be maintained using tertiary amines only.

STORAGE STABILITY

CYTEL 325 N resin has a shelf life of 720 days from the date of manufacture when stored at temperatures between 5°C and 25°C. Although lower temperatures are not detrimental to stability, its viscosity will increase, possibly making the resin difficult to pump or pour. The viscosity will reduce again on warming, but care should be taken to avoid excessive local heat as this can cause an irreversible increase in viscosity.